

## H1,5/7

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



- For conductors from 0.25 to 6,0 mm<sup>2</sup> (AWG 24 - 10)  
 tin-plated copper  
 dimensional tolerances to DIN 46228 part 1
- supplied loose in polybag

### General ordering data

Version	Wire-end ferrule, Standard, 7 mm, 7 mm, No
Order No.	<a href="#">0372700000</a>
Type	H1,5/7
GTIN (EAN)	4008190064525
Qty.	1,000 pc(s).
Packaging	loose

## H1,5/7

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight 0.052 g

## Technical data

Description of article	Wire end ferrule without plastic collar	Version	Standard
------------------------	---	---------	----------

## Wire-end ferrules

Collar diameter (D2)	2.8 mm	Conductor cross-section	1.5 mm <sup>2</sup>
Contact surface diameter (D1)	1.7 mm	Contact surface length (L2)	7 mm
L1 in mm	7 mm	Stripping length	7 mm
Wire connection cross section AWG, max.	AWG 16		

## Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**Data sheet**

**H1,5/7**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Drawings**

