

IH 2.8 DB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

With insulating sleeve for cable lug, an increase of the rated voltage within the application is possible.

General ordering data

Version	W-Series, Insulating sleeve
Order No.	0386060000
Type	IH 2.8 DB
GTIN (EAN)	4008 190043414
Qty.	100 pc(s).

Creation date March 6, 2023 1:13:54 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

IH 2.8 DB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	5.1 mm	Depth (inches)	0.201 inch
Height	18 mm	Height (inches)	0.709 inch
Width	3.6 mm	Width (inches)	0.142 inch
Net weight	0.18 g		

Temperatures

Storage temperature	-25 °C...55 °C	Operating temperature	-50 °C...
Operating temperature, min.	-50 °C	Continuous operating temp., max.	120 °C

Material data

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
--------------------------	----	---------------------	-----------------

General

Installation advice	Direct mounting
---------------------	-----------------

UL rating data

Certificate No. (UR)	E60693
----------------------	--------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E60693

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format