

**MB M3/M5 CRM**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Product image**



Mounting feet are used to mount components that cannot be snapped directly on a DIN rail.

**General ordering data**

Version	Accessories, Sliding nut, Polyamide 66
Order No.	<a href="#">0503500000</a>
Type	MB M3/M5 CRM
GTIN (EAN)	4008190182083
Qty.	20 Stück

## MB M3/M5 CRM

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	14 mm	Depth (inches)	0.551 inch
Height	25 mm	Height (inches)	0.984 inch
Width	12 mm	Width (inches)	0.472 inch
Net weight	3.55 g		

### Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

### Material data

Material	Polyamide 66	Surface finish	untreated
Colour	Cream	UL 94 flammability rating	V-2

### System specifications

Version	For the mounting rails	Rail	TS 32
---------	------------------------	------	-------

### Additional technical data

Explosion-tested version	No	Type of fixing	Snap-on
--------------------------	----	----------------	---------

### Dimensions

Internal thread	M 5	Metric size of the thread, external	0 M3.0
Pitch in mm (P)	12 mm		

### General

Rail	TS 32	Surface finish	untreated
------	-------	----------------	-----------

### Classifications

ETIM 6.0	EC000096	ETIM 7.0	EC000096
ETIM 8.0	EC000096	ECLASS 9.0	23-11-08-04
ECLASS 9.1	23-11-08-04	ECLASS 10.0	23-11-08-04
ECLASS 11.0	23-11-07-16	ECLASS 12.0	23-11-07-16

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">WSCAD, EPLAN</a>
User Documentation	<a href="#">Storage Conditions</a> <a href="#">Terminal Blocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">CAT 1 TERM 16/17 EN</a>