

**G 25/0.50A/M WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

For protection against overcurrent, we offer cartridge fuse with dimensions 5x25 mm in sizes from 250 mA to 6.3 A.

**General ordering data**

Version	Active components, Fuse
Order No.	<a href="#">0510300000</a>
Type	G 25/0.50A/M WS
GTIN (EAN)	4008 1900 18368
Qty.	10 pc(s).

## G 25/0.50A/M WS

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	5 mm	Depth (inches)	0.197 inch
Height	25 mm	Height (inches)	0.984 inch
Width	5 mm	Width (inches)	0.197 inch
Net weight	1.18 g		

### Material data

Colour	Light Grey
--------	------------

### System specifications

Version	Fuse accessories
---------	------------------

### Fuse cartridges

Cartridge fuse	G-Si. 5 x 25	Characteristics	medium time-lag
Colour	Light Grey	Colour of the indicator	white
Current	0.5 A	Melting integral	1.1 A <sup>2</sup> s
Optical function display	Yes	Power output (@ 1.5 In)	0.2 W
Rated breaking capacity	1.5 kA	Version	Fuse accessories
Voltage drop	250 mV		

### Rating data

Rated voltage	250 V	Rated current	0.5 A
---------------	-------	---------------	-------

### Classifications

ETIM 6.0	EC000035	ETIM 7.0	EC000035
ETIM 8.0	EC002704	ECLASS 9.0	27-14-20-01
ECLASS 9.1	27-14-20-01	ECLASS 10.0	27-14-20-01
ECLASS 11.0	27-14-20-01	ECLASS 12.0	27-14-20-01

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Cadmium 7440-43-9
SCIP	6293d729-7239-4261-a7e8-f82a539a372e

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">WSCAD</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	