

MB M5/M3 SW

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Product image



Similar to illustration

Mounting feet are used to mount components that cannot be snapped directly on a DIN rail.

General ordering data

Version	Accessories, Sliding nut, Polyamide 66
Order No.	0553400000
Type	MB M5/M3 SW
GTIN (EAN)	4008190122263
Qty.	20 Stück

MB M5/M3 SW

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	14 mm	Depth (inches)	0.551 inch
Height	25 mm	Height (inches)	0.984 inch
Width	12 mm	Width (inches)	0.472 inch
Net weight	3.5 g		

Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

Material data

Material	Polyamide 66	Surface finish	untreated
Colour	black	UL 94 flammability rating	V-2

System specifications

Version	For the mounting rails	Rail	TS 32
---------	------------------------	------	-------

Additional technical data

Explosion-tested version	No	Type of fixing	Snap-on
--------------------------	----	----------------	---------

Dimensions

Internal thread	M 5	Metric size of the thread, external	0 M5.0
Pitch in mm (P)	12 mm		

General

Rail	TS 32	Surface finish	untreated
------	-------	----------------	-----------

Classifications

ETIM 6.0	EC000096	ETIM 7.0	EC000096
ETIM 8.0	EC000096	ECLASS 9.0	23-11-08-04
ECLASS 9.1	23-11-08-04	ECLASS 10.0	23-11-08-04
ECLASS 11.0	23-11-07-16	ECLASS 12.0	23-11-07-16

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD, EPLAN
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	CAT 1 TERM 16/17 EN