

**KLBU SH1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

Version	Accessories, Clamping yoke
Order No.	<a href="#">0635900000</a>
Type	KLBU SH1
GTIN (EAN)	4008190192204
Qty.	500 Stück

## KLBUE SH1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	16 mm	Depth (inches)	0.63 inch
Height	26.5 mm	Height (inches)	1.043 inch
Width	15 mm	Width (inches)	0.591 inch
Net weight	1.88 g		

### Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

### Material data

Colour	dark beige
--------	------------

### System specifications

Version	For the rail holder
---------	---------------------

### Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting, Busbar
Type of fixing	Snap-on		

### Dimensions

Pitch in mm (P)	16 mm
-----------------	-------

### General

Installation advice	Direct mounting, Busbar
---------------------	-------------------------

### Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ECLASS 9.0	27-14-11-50
ECLASS 9.1	27-14-11-50	ECLASS 10.0	27-14-11-50
ECLASS 11.0	27-14-11-50	ECLASS 12.0	27-14-11-50

### Approvals

Approvals	
-----------	---

ROHS	Conform
------	---------

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">EAC certificate</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>