

KLBU SH1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	Accessories, Clamping yoke
Order No.	0635960000
Type	KLBU SH1
GTIN (EAN)	4008 190007 140
Qty.	20 Stück

Erstellungs-Datum May 26, 2023 5:39:29 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

KLBUE SH1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	16 mm	Depth (inches)	0.63 inch
Height	26.5 mm	Height (inches)	1.043 inch
Width	15 mm	Width (inches)	0.591 inch
Net weight	1.685 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Colour	dark beige
--------	------------

System specifications

Version	For the rail holder
---------	---------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting, Busbar
Type of fixing	Snap-on		

Dimensions

Pitch in mm (P)	16 mm
-----------------	-------

General

Installation advice	Direct mounting, Busbar
---------------------	-------------------------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ECLASS 9.0	27-14-11-50
ECLASS 9.1	27-14-11-50	ECLASS 10.0	27-14-11-50
ECLASS 11.0	27-14-11-50	ECLASS 12.0	27-14-11-50

Approvals

Approvals	
-----------	---

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	EAC certificate
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	CAT 1 TERM 16/17 EN