

**CLI O 30-3 GE/SW - MP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

CLI O conductor markers are fitted to connected conductors, and are therefore suitable for updating existing systems. Without problems, three different sizes can be used for marking conductor cross-sections from 0.4 mm<sup>2</sup> to max. 4.0 mm<sup>2</sup>. The shape and design guarantee secure and permanent attachment of the individually combinable markers.

**Advantages:**

- Open markers for connected conductors
- Marker version with anti-rotation safeguard for secure combination marking
- Perfect for any supplementary labelling
- Extremely low space requirements
- Rapid clip-on attachment saves time

**General ordering data**

|            |  |
|------------|--|
| Version    | CableLine, Conductor and cable markers, 4 - 5 mm, 3 x 6 mm, yellow |
| Order No.  | <a href="#">0648201740</a>   |
| Type       | CLI O 30-3 GE/SW - MP  |
| GTIN (EAN) | 4032248456178  |
| Qty.       | 200 pc(s).   |

## CLI O 30-3 GE/SW - MP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 6 mm   | Depth (inches)  | 0.236 inch |
| Height     | 3 mm   | Height (inches) | 0.118 inch |
| Width      | 6 mm   | Width (inches)  | 0.236 inch |
| Net weight | 0.04 g |                 |            |

### Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

### General data

|  |                    |                                   |                            |
|--|--------------------|-----------------------------------|----------------------------|
| Colour                                       | yellow             | Colour of printing                | black                      |
| Halogen                                      | Yes                | Material                          | PVC, soft, without Cadmium |
| Material colour according to resistance code | 4                  | Operating temperature range       | -30...80 °C                |
| Operating temperature range, max.            | 80 °C              | Operating temperature range, min. | -30 °C                     |
| Orientation of print                         | horizontal         | Printed characters                | Symbols                    |
| Printing                                     | -                  | Printing method                   | hot-embossing              |
| Recommended industries                       | Process, Machinery | Type of printing                  | Standard                   |
| UL 94 flammability rating                    | V-0                | Version                           | MultiPack                  |
| Width  | 6 mm               |                                   |                            |

### Conductor and cable markers

|                               |                   |                                  |                       |
|-------------------------------|-------------------|----------------------------------|-----------------------|
| Conductor O.D.                | 4 - 5 mm          | Conductor O.D., max.             | 5 mm                  |
| Conductor O.D., min.          | 4 mm              | Conductor cross-section, max.    | 4 mm <sup>2</sup>     |
| Conductor cross-section, min. | 3 mm <sup>2</sup> | Cross-section for connected wire | 3 - 4 mm <sup>2</sup> |
| Halogen                       | Yes               |                                  |                       |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">WSCAD</a>                    |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

**Data sheet**

**CLI O 30-3 GE/SW - MP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



Similar to illustration