

**KSWF M20**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Similar to illustration**



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	KSWF (flat gasket - vulcanised fibre). Sealing ring, M 20, Vulcanized fibre
Order No.	<a href="#">0899750000</a>
Type	KSWF M20
GTIN (EAN)	4032248850174
Qty.	25 Stück

Erstellungs-Datum May 25, 2023 12:14:26 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## KSWF M20

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Net weight 0.68 g

### Temperatures

Operating temperature	-40 °C...95 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	95 °C		

### General information

Cable glands	M 20	Diameter of sealing ring	29.4 mm
External thread	M 20	Inside diameter D2	20.7 mm
Material	Vulcanized fibre	Number of wires	1
Operating temperature range, max.	95 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5 mm	Silicone	No

### Classifications

ETIM 6.0	EC001181	ETIM 7.0	EC001181
ETIM 8.0	EC001181	ECLASS 9.0	27-43-03-19
ECLASS 9.1	27-14-44-90	ECLASS 10.0	27-43-03-19
ECLASS 11.0	27-43-03-19	ECLASS 12.0	27-43-03-19

### Approvals

ROHS Conform

### Downloads

Engineering Data	<a href="#">WSCAD, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**KSWF M20**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

