

KSWN M40**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	KSWN (flat gasket - nylon), Sealing ring, M 40, Nylon 6
Order No.	0899780000
Type	KSWN M40
GTIN (EAN)	4032248850150
Qty.	25 Stück

KSWN M40

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 1.68 g

Temperatures

Operating temperature	-40 °C... 135 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	135 °C		

General information

Cable glands	M 40	Diameter of sealing ring	52 mm
External thread	M 40	Inside diameter D2	40.5 mm
Material	Nylon 6	Number of wires	1
Operating temperature range, max.	135 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5 mm	Silicone	No

Classifications

ETIM 6.0	EC001181	ETIM 7.0	EC001181
ETIM 8.0	EC001181	ECLASS 9.0	27-43-03-19
ECLASS 9.1	27-14-44-90	ECLASS 10.0	27-43-03-19
ECLASS 11.0	27-43-03-19	ECLASS 12.0	27-43-03-19

Approvals

ROHS Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format
Brochures	

KSWN M40

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

