

SKMU M40 MS SC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	SKMU MS (brass locknut), Locknut, M 40, 4.8 mm, Brass
Order No.	0930640005
Type	SKMU M40 MS SC
GTIN (EAN)	4032248976096
Qty.	10 Stück

Erstellungs-Datum May 25, 2023 12:15:34 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

SKMU M40 MS SC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 21.8 g

General information

AF size 1	46 mm	Cable glands	M 40
External thread	M 40	Halogen	No
Internal thread	M 40	Length of thread	4.8 mm
Material	Brass	Pitch of thread	1.5 mm
Thickness	4.8 mm		

Classifications

ETIM 6.0	EC000940	ETIM 7.0	EC000940
ETIM 8.0	EC000940	ECLASS 9.0	27-14-44-24
ECLASS 9.1	27-14-44-24	ECLASS 10.0	27-14-44-24
ECLASS 11.0	27-14-44-24	ECLASS 12.0	27-14-08-05

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Approvals

ROHS Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format
Brochures	

Datenblatt

SKMU M40 MS SC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

