

**SKMU M75 MS SC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	SKMU MS (brass locknut), Locknut, M 75, 7 mm, Brass
Order No.	<a href="#">0930640008</a>
Type	SKMU M75 MS SC
GTIN (EAN)	4032248976126
Qty.	5 Stück

Erstellungs-Datum May 25, 2023 12:16:00 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## SKMU M75 MS SC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Net weight 149 g

### General information

AF size 1	90 mm	Cable glands	M 75
External thread	M 75	Halogen	No
Internal thread	M 75	Length of thread	7 mm
Material	Brass	Pitch of thread	1.5 mm
Thickness	7 mm		

### Classifications

ETIM 6.0	EC000940	ETIM 7.0	EC000940
ETIM 8.0	EC000940	ECLASS 9.0	27-14-44-24
ECLASS 9.1	27-14-44-24	ECLASS 10.0	27-14-44-24
ECLASS 11.0	27-14-44-24	ECLASS 12.0	27-14-08-05

### Environmental Product Compliance

REACH SVHC Lead 7439-92-1

### Approvals

ROHS Conform

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**Datenblatt**

**SKMU M75 MS SC**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

