

**IE-PS-V01P-RJ45-TH-BP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Bayonet plug-in connector sets according to IEC  
61076-3-106 ver.1 (EtherNet/IP), RJ45 plastic insert incl.  
RJ45 insert

**General ordering data**

Version	RJ45 crimp plug, Variant 1 plastic, with kink prevention, Cat.6A / Class EA (ISO/IEC 11801 2010)
Order No.	<a href="#">1012560000</a>
Type	IE-PS-V01P-RJ45-TH-BP
GTIN (EAN)	4032248720194
Qty.	10 pc(s).

Creation date February 28, 2023 4:34:59 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

## IE-PS-V01P-RJ45-TH-BP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight 40.2 g

## Temperatures

Operating temperature	-40 °C...70 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	70 °C		

## General data

Connection 1	RJ45	Connection 2	Crimp
Description of article	Variant 1 plastic, with kink prevention	Colour	black
Housing main material	PA UL 94 V0	Insulation cross-section, min.	0.85 mm
Insulation cross-section, max.	1.05 mm	Category	Cat.6A / Class EA (ISO/IEC 11801 2010)
Contact surface	Gold over nickel	Connection diameter, solid	0.36...0.51 mm
Conductor connection cross-section, solid (AWG)	AWG 26/1...AWG 24/1	Connection diameter, flexible	0.46...0.61 mm
Conductor connection cross-section, flexible (AWG)	AWG 27/7...AWG 24/7	MICE classification M	M <sub>3</sub>
MICE classification I	I <sub>3</sub>	MICE classification C	C <sub>1</sub>
MICE classification E	E <sub>3</sub>	Sheath diameter, min.	5 mm
Sheath diameter, max.	10 mm	Shielding	360°deg; all-round enclosure
Protection degree	IP67	Plugging cycles	750

## General standards

Certificate no. (cULus)	E316369	Connector standard	IEC 61076-3-106 Var. 1, IEC 60603-7-51
-------------------------	---------	--------------------	--

## Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ECLASS 9.0	27-44-03-90
ECLASS 9.1	27-44-03-90	ECLASS 10.0	27-44-03-90
ECLASS 11.0	27-44-03-90	ECLASS 12.0	27-44-03-90

## Environmental Product Compliance

REACH SVHC	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	11b17e97-f803-4c09-9278-b20f22f15f81

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E316369

**IE-PS-V01P-RJ45-TH-BP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Downloads**

Approval/Certificate/Document of Conformity	<a href="#">ISO/IEC and TIA/EIA DE DUXR.E316369</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
Product Change Notification	<a href="#">20210412 Technical change for cap nut V1 and V4</a> <a href="#">20210412 Technische Änderung zu Hutmutter V1 und V4</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a> <a href="#">Manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">MB FREECONTACT EN</a> <a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>

**Data sheet**

**IE-PS-V01P-RJ45-TH-BP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Dimensioned drawing**

