

SFC 1/30 MC NE GR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration



The SlimFix Clip combines two advantages: its unique closure mechanism offers the reliability of a closed marker with the ease of installation of an open marker. The clip mechanism allows quick and convenient installation of the marker even after the conductor has been installed. SlimFix Clips are suitable for conductors and cables with an outside diameter of up to 5 mm. The large marking surface - up to 30 mm - enables long character strings. The material is halogen-free and complies with flammability rating V2.

Advantages:

- Halogen-free material
- Flammability rating V2
- Fast installation without tools
- Markers in proven MultiCard format
- Available in the heights of 12 mm, 21 mm and 30 mm

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|--------------------|--|
| Version | SlimFix Clip, Conductor and cable markers, 2 - 3.5 mm, 30 x 5.8 mm, grey |
| Order No. | 1014660000 |
| Type | SFC 1/30 MC NE GR |
| GTIN (EAN) | 4032248723348 |
| Qty. | 150 pc(s). |
| compatible printer | 2715590000 2438520000 2438510000 |

SFC 1/30 MC NE GR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 7 mm | Depth (inches) | 0.276 inch |
| Height | 30 mm | Height (inches) | 1.181 inch |
| Width | 5.8 mm | Width (inches) | 0.228 inch |
| Net weight | 0.64 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

General data

| | | | |
|-----------------------------------|---|--|--------------|
| Colour | grey | Halogen | No |
| Material | Polyamide 66 | Material colour according to resistance code | 5 |
| Number of markers per combination | 1 MultiCard = Conductor and cable markers | Operating temperature range | -40...100 °C |
| Operating temperature range, max. | 100 °C | Operating temperature range, min. | -40 °C |
| Recommended industries | Machinery | Size of labelling field | 30 x 4.1 mm |
| Type of printing | neutral | UL 94 flammability rating | V-2 |
| Width | 5.8 mm | | |

Conductor and cable markers

| | | | |
|-------------------------------|----------------------|----------------------------------|----------------------------|
| Conductor O.D. | 2 - 3.5 mm | Conductor O.D., max. | 3.5 mm |
| Conductor O.D., min. | 2 mm | Conductor cross-section, max. | 2.5 mm ² |
| Conductor cross-section, min. | 0.75 mm ² | Cross-section for connected wire | 0.75 - 2.5 mm ² |
| Halogen | No | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, Zuken E3.S |
| Catalogues | Catalogues in PDF-format |

Data sheet

SFC 1/30 MC NE GR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

