

WQL 4 WF10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	Bolt-type screw terminals, Cross-connector, Number of poles: 4
Order No.	1027840000
Type	WQL 4 WF10
GTIN (EAN)	4032248779956
Qty.	5 pc(s).

Creation date February 28, 2023 12:08:24 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

WQL 4 WF10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	4 mm	Depth (inches)	0.157 inch
Height	129.4 mm	Height (inches)	5.094 inch
Width	25 mm	Width (inches)	0.984 inch
Net weight	98 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Copper - zinc	Colour	grey
----------	---------------	--------	------

Additional technical data

Type of fixing	when screwed in
----------------	-----------------

Cross-connector

Rated current, multi-pole	265 A
---------------------------	-------

Dimensions

Pitch in mm (P)	33.8 mm
-----------------	---------

General

Number of poles	4
-----------------	---

Rating data

Rated current	265 A
---------------	-------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	