

## VG16 HQ K68 9-12SH

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

### General ordering data

Version	Heavy-duty connectors, Accessories, Cable glands, Polycarbonate
Order No.	<a href="#">1045530000</a>
Type	VG16 HQ K68 9-12SH
GTIN (EAN)	4032248779437
Qty.	50 pc(s).

Creation date March 7, 2023 2:40:46 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

## VG16 HQ K68 9-12SH

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	0.245 g
------------	---------

## Temperatures

Limit temperature	-20 °C ... 100 °C
-------------------	-------------------

## General information

AF size	30 mm	Cable glands	PG 16
External thread	PG 16	Material	Polycarbonate
Protection degree	IP68		

## Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32	ECLASS 12.0	27-14-08-01

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
Product Change Notification	<a href="#">20210205 Technical change to HQ Cable Glands</a> <a href="#">20210205 Technische Änderung zu HQ Kabelverschraubung</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>