

IE-OP-V04P-1S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Junction box, design for PushPull plug-in connectors ver.4
according to IEC 61076-3-106, plastic

General ordering data

Version	Wall-mounted junction box, IP67, Variant 4 to IEC 61076-3-106
Order No.	1045780000
Type	IE-OP-V04P-1S
GTIN (EAN)	4032248779963
Qty.	10 pc(s).

Creation date February 20, 2023 4:22:34 PM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

IE-OP-V04P-1S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	106.9 mm	Depth (inches)	4.209 inch
Height	61.6 mm	Height (inches)	2.425 inch
Width	41.8 mm	Width (inches)	1.646 inch
Net weight	6.5 g		

Temperatures

Operating temperature	-40 °C...70 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	70 °C		

General data

Colour	black	Housing main material	PA
Plugging cycles	750	Protection degree	IP67
Type of mounting	Floor-mounted, for exposed connections, Wall mounting	UL 94 flammability rating	V-0

General standards

Connector standard	IEC 61076-3-106 Var. 4
--------------------	------------------------

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ECLASS 9.0	27-44-02-02
ECLASS 9.1	27-44-03-92	ECLASS 10.0	27-44-02-02
ECLASS 11.0	27-44-02-02	ECLASS 12.0	27-44-02-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	MB FREECONTACT EN FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-OP-V04P-1S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing

