

**WQV 16/2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	W-Series, Cross-connector, For the terminals, Number of poles: 2
Order No.	<a href="#">1053260000</a>
Type	WQV 16/2
GTIN (EAN)	4008 190036553
Qty.	50 pc(s).

Creation date March 1, 2023 11:53:55 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

## WQV 16/2

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	27 mm	Depth (inches)	1.063 inch
Height	21.4 mm	Height (inches)	0.843 inch
Width	10.4 mm	Width (inches)	0.409 inch
Net weight	7.36 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

## Material data

Material	PA 66	Colour	yellow
UL 94 flammability rating	V-0		

## System specifications

Version	For the terminals
---------	-------------------

## Additional technical data

Installation advice	Direct mounting	Type of fixing	when screwed in
---------------------	-----------------	----------------	-----------------

## Cross-connector

Number of cross-connected terminals	2	Rated current, 2-pole	101 A
Rated current, multi-pole	101 A	Tightening torque range for fixing screw	1.2...2.4 Nm
Type	Cross-connector		

## Dimensions

Pitch in mm (P)	11.9 mm
-----------------	---------

## General

Installation advice	Direct mounting	Number of poles	2
---------------------	-----------------	-----------------	---

## Rating data

Rated current	101 A
---------------	-------

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

**WQV 16/2**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Approvals**

Approvals



ROHS

Conform

**Downloads**

Approval/Certificate/Document of  
Conformity

[EAC certificate](#)

Engineering Data

[CAD data – 08874\\_WQV\\_16-2\\_DXF.dxf](#)  
[CAD data – STEP](#)

Engineering Data

[WSCAD\\_Zuken E3.S](#)

User Documentation

[Beipackzettel\\_WQV.pdf](#)  
[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures