

## IE-BP-V14P

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



For protecting your devices against dust and dirt.

### General ordering data

Version	Flange-mounted housing, protective cap
Order No.	<a href="#">1058310000</a>
Type	IE-BP-V14P
GTIN (EAN)	4032248799404
Qty.	10 Stück

## IE-BP-V14P

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	22.9 mm	Depth (inches)	0.902 inch
Net weight	4.778 g		

### Temperatures

Operating temperature	-40 °C...70 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	70 °C		

### General data

Colour	black	Housing main material	PA UL 94 V0
Protection degree	IP67	Type of mounting	Indoors only
UL 94 flammability rating	V-0		

### Classifications

ETIM 6.0	EC002314	ETIM 7.0	EC002314
ETIM 8.0	EC002314	ECLASS 9.0	27-44-02-08
ECLASS 9.1	27-44-02-08	ECLASS 10.0	27-44-02-08
ECLASS 11.0	27-44-02-08	ECLASS 12.0	27-44-02-08

### Environmental Product Compliance

REACH SVHC	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	11b17e97-f803-4c09-9278-b20f22f15f81

### Approvals

Approvals



ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">WSCAD, Zuken E3.S, EPLAN</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>