

CB-R 250/7,5 NC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

Similar to illustration

Releasable and reusable cable ties, suitable for temporary bundling and when open-close function is necessary.

General ordering data

Version	Cable ties, 7.5 x 250 mm, Polyamide 66, 220 N
Order No.	1059220000
Type	CB-R 250/7,5 NC
GTIN (EAN)	4032248806164
Qty.	100 Stück

Erstellungs-Datum May 26, 2023 5:45:58 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

CB-R 250/7,5 NC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	2 mm	Depth (inches)	0.079 inch
Height	250 mm	Height (inches)	9.842 inch
Width	7.5 mm	Width (inches)	0.295 inch
Net weight	2.58 g		

Temperatures

Operating temperature range	-40...85 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	85 °C		

Installation materials

Bundle diameter, max.	65 mm	Bundle diameter, min.	3 mm
Cable diameter, max.	70 mm	For re-opening	Yes
Halogen	No	Material	Polyamide 66
Operating temperature range, max.	85 °C	Operating temperature range, min.	-40 °C
Tensile strength	220 N	Tensile strength (Pound-force)	49 lbf
UL 94 flammability rating	V-2	UV-resistant	No

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02	ECLASS 12.0	27-14-07-02

Approvals

Approvals



ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	DE P1830000 160627 001
Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format

CB-R 250/7,5 NC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Zeichnungen

www.weidmueller.com

Drawing

