

**CB-R 250/7,5 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Releasable and reusable cable ties, suitable for temporary bundling and when open-close function is necessary.

**General ordering data**

Version	Cable ties, 7.5 x 250 mm, Polyamide 66, 220 N
Order No.	<a href="#">1059230000</a>
Type	CB-R 250/7,5 BK
GTIN (EAN)	4032248806171
Qty.	100 Stück

Erstellungs-Datum May 26, 2023 5:46:07 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## CB-R 250/7,5 BK

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	2 mm	Depth (inches)	0.079 inch
Height	250 mm	Height (inches)	9.842 inch
Width	7.5 mm	Width (inches)	0.295 inch
Net weight	2.56 g		

### Temperatures

Operating temperature range	-40...85 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	85 °C		

### Installation materials

Bundle diameter, max.	65 mm	Bundle diameter, min.	3 mm
Cable diameter, max.	70 mm	For re-opening	Yes
Halogen	No	Material	Polyamide 66
Operating temperature range, max.	85 °C	Operating temperature range, min.	-40 °C
Tensile strength	220 N	Tensile strength (Pound-force)	49 lbf
UL 94 flammability rating	V-2	UV-resistant	No

### Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02	ECLASS 12.0	27-14-07-02

### Approvals

Approvals



ROHS Conform

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">DE PI830000_160627_001</a>
Engineering Data	<a href="#">WSCAD, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Datenblatt**

**CB-R 250/7,5 BK**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

**Drawing**

