

THM GEW 17/9 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



THM GEW woven-fabric labels are made from a very flexible cotton fabric. Delivery on reels for use with thermal transfer printers enables an adhesive layer which is thicker than that of A4 sheets for office laser printers. Together, this flexibility and the thick adhesive layer ensure higher adhesive strength and enable use on angular or round objects such as e.g. cables or hoses.

General ordering data

| | |
|--------------------|---|
| Version | THM, Device markers, 9 x 17 mm, white |
| Order No. | 1059800000 |
| Type | THM GEW 17/9 WS |
| GTIN (EAN) | 4032248808199 |
| Qty. | 1 pc(s). |
| compatible printer | 2599430000 2599440000 |

Creation date May 4, 2023 5:06:54 PM CEST

Catalogue status 28.04.2023 / We reserve the right to make technical changes.

THM GEW 17/9 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 0.3 mm | Depth (inches) | 0.012 inch |
| Height | 9 mm | Height (inches) | 0.354 inch |
| Width | 17 mm | Width (inches) | 0.669 inch |
| Net weight | 642 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -29...80 °C |
|-----------------------------|-------------|

General data

| | | | |
|-----------------------------------|-------------------------------|--|-------------|
| Adhesive | Natural rubber adhesive | Approval acc. to UL 969 | No |
| Colour | white | Halogen | No |
| Material | Cotton fabric | Material colour according to resistance code | 9 |
| Number of markers per combination | 1 Label reel = Device markers | Number per roll | 10,000 |
| Number per sheet | 10,000 | Operating temperature range | -29...80 °C |
| Operating temperature range, max. | 80 °C | Operating temperature range, min. | -29 °C |
| Printing method | Thermal transfer | UL 94 flammability rating | V-0 |
| Version | Self-adhesive | Width | 17 mm |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ECLASS 9.0 | 27-40-06-29 |
| ECLASS 9.1 | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD |
| Catalogues | Catalogues in PDF-format |

Data sheet

THM GEW 17/9 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



