

WQV 120/3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image**Power feed-in**

Our wide range of W-Series terminal blocks with our WPD main line branch terminals, which are optimised to guarantee both convenience and space gains, ensures a secure and convenient connection at the power feed-in.

General ordering data

| | |
|------------|---|
| Version | W-Series, Cross-connector, For the terminals, Number of poles: 3 |
| Order No. | 1063400000 |
| Type | WQV 120/3 |
| GTIN (EAN) | 4008190141363 |
| Qty. | 5 pc(s). |

Creation date February 28, 2023 12:03:55 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

WQV 120/3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 71.8 mm | Depth (inches) | 2.827 inch |
| Height | 76 mm | Height (inches) | 2.992 inch |
| Width | 10 mm | Width (inches) | 0.394 inch |
| Net weight | 224.2 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 100 °C | | |

Material data

| | | | |
|---------------------------|-------|--------|-------------|
| Material | PA 66 | Colour | Silver grey |
| UL 94 flammability rating | V-2 | | |

System specifications

| | |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

Additional technical data

| | | | |
|---------------------|-----------------|----------------|-----------------|
| Installation advice | Direct mounting | Type of fixing | when screwed in |
|---------------------|-----------------|----------------|-----------------|

Cross-connector

| | | | |
|-------------------------------------|-------|-----------------------|-----------------|
| Number of cross-connected terminals | 3 | Rated current, 2-pole | 269 A |
| Rated current, multi-pole | 269 A | Type | Cross-connector |

Dimensions

| | |
|-----------------|-------|
| Pitch in mm (P) | 32 mm |
|-----------------|-------|

General

| | | | |
|---------------------|-----------------|-----------------|---|
| Installation advice | Direct mounting | Number of poles | 3 |
|---------------------|-----------------|-----------------|---|

Rating data

| | |
|---------------|-------|
| Rated current | 292 A |
|---------------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 |
| ETIM 8.0 | EC000489 | ECLASS 9.0 | 27-14-11-40 |
| ECLASS 9.1 | 27-14-11-40 | ECLASS 10.0 | 27-14-11-40 |
| ECLASS 11.0 | 27-14-11-40 | ECLASS 12.0 | 27-14-11-40 |

Approvals

Approvals



ROHS Conform

Creation date February 28, 2023 12:03:55 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

WQV 120/3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Downloads**

| | |
|---|---|
| Approval/Certificate/Document of Conformity | EAC certificate |
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, Zuken E3.S |
| User Documentation | StorageConditionsTerminalBlocks Instruction |
| Catalogues | Catalogues in PDF-format |
| Brochures | |