

**WZAD 70/95****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image****General ordering data**

|            |                                 |
|------------|---------------------------------|
| Version    | W-Series, Additional connection |
| Order No.  | <a href="#">1066000000</a>      |
| Type       | WZAD 70/95                      |
| GTIN (EAN) | 4008 1900 17064                 |
| Qty.       | 10 pc(s).                       |

Creation date March 3, 2023 4:44:00 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

## WZAD 70/95

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 10 mm    | Depth (inches)  | 0.394 inch |
| Height     | 39.61 mm | Height (inches) | 1.559 inch |
| Width      | 19.7 mm  | Width (inches)  | 0.776 inch |
| Net weight | 6.05 g   |                 |            |

### Temperatures

|                     |                |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

### Material data

|          |               |        |             |
|----------|---------------|--------|-------------|
| Material | tinned copper | Colour | Silver grey |
|----------|---------------|--------|-------------|

### System specifications

|                                     |                       |                  |   |
|-------------------------------------|-----------------------|------------------|---|
| Version                             | Additional connection | Number of levels | 1 |
| Number of clamping points per level | 1                     |                  |   |

### Additional technical data

|                          |         |                     |  |
|--------------------------|---------|---------------------|--|
| Explosion-tested version | No      | Installation advice | Feed-through (bushing),<br>Direct mounting |
| Type of fixing           | Snap-on |                     |  |

### Conductors for clamping (rated connection)

|                       |   |
|-----------------------|---|
| Number of connections | 1 |
|-----------------------|---|

### Dimensions

|                 |       |
|-----------------|-------|
| Pitch in mm (P) | 20 mm |
|-----------------|-------|

### General

|                     |  |
|---------------------|--|
| Installation advice | Feed-through (bushing),<br>Direct mounting |
|---------------------|--|

### Rating data

|               |      |
|---------------|------|
| Rated current | 32 A |
|---------------|------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002848    | ETIM 7.0    | EC002848    |
| ETIM 8.0    | EC002848    | ECLASS 9.0  | 27-14-11-92 |
| ECLASS 9.1  | 27-14-11-92 | ECLASS 10.0 | 27-14-11-92 |
| ECLASS 11.0 | 27-14-11-92 | ECLASS 12.0 | 27-14-11-92 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**WZAD 70/95**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Downloads**

---

|                    |   |
|--------------------|---|
| Engineering Data   | <a href="#">CAD data – STEP</a>                 |
| Engineering Data   | <a href="#">WSCAD, Zuken E3.S</a>               |
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>        |
| Brochures          |   |

---