

## IE-PI-SCRJ-SM

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



FO SC inserts for plug-in connectors ver.1 / 4 / 14

### General ordering data

Version	SC insert, Plug SCRJ, singlemode
Order No.	<a href="#">1067390000</a>
Type	IE-PI-SCRJ-SM
GTIN (EAN)	4032248820863
Qty.	10 Stück

Erstellungs-Datum May 25, 2023 12:18:32 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## IE-PI-SCRJ-SM

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	56 mm	Depth (inches)	2.205 inch
Height	10.5 mm	Height (inches)	0.413 inch
Width	13.2 mm	Width (inches)	0.52 inch
Net weight	19.4 g		

### Temperatures

Operating temperature	-40 °C...70 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	70 °C		

### General data

Colour	Miscellaneous	Configuration	Connector and flange insert for variant 1, 4 and 14 housings
Connection 1	SCRJ	Connection 2	Crimp
Description of article	Plug SCRJ, singlemode	Ferrule material	Zirconia
Fibre type	Singlemode	Housing main material	Zinc diecast, PA
Insertion loss	≤ 0.5 dB	Plugging cycles	1000
Protection degree	IP67 with housing	Return loss (attenuation)	≥ 40 dB

### General standards

Certificate No. (UL)	E477798	Connector standard	IEC 61754-24
----------------------	---------	--------------------	--------------

### Classifications

ETIM 6.0	EC001122	ETIM 7.0	EC001122
ETIM 8.0	EC001122	ECLASS 9.0	19-17-01-22
ECLASS 9.1	19-17-01-22	ECLASS 10.0	19-17-01-22
ECLASS 11.0	19-17-01-22	ECLASS 12.0	19-17-01-22

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

### Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UL)	E477798

## IE-PI-SCRJ-SM

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">PROFINET Manufacturer's Declaration</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a> <a href="#">Designation key / Type key</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>

**IE-PI-SCRJ-SM**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

**Dimensioned drawing**

