

## IE-BP-VAPP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



For protecting your devices against dust and dirt.

### General ordering data

Version	Flange-mounted housing, protective cap
Order No.	<a href="#">1068930000</a>
Type	IE-BP-VAPP
GTIN (EAN)	4032248823093
Qty.	10 Stück

Erstellungs-Datum May 26, 2023 5:46:53 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## IE-BP-VAPP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	19.5 mm	Depth (inches)	0.768 inch
Net weight	11 g		

### Temperatures

Operating temperature	-40 °C...70 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	70 °C		

### General data

Colour	black	Protection degree	IP54
Type of mounting	Indoors only	UL 94 flammability rating	V-0

### Classifications

ETIM 6.0	EC002314	ETIM 7.0	EC002314
ETIM 8.0	EC002314	ECLASS 9.0	27-44-02-08
ECLASS 9.1	27-44-02-08	ECLASS 10.0	27-44-02-08
ECLASS 11.0	27-44-02-08	ECLASS 12.0	27-44-02-08

### Approvals

Approvals



ROHS Conform

### Downloads

Engineering Data	<a href="#">WSCAD</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>

## IE-BP-VAPP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Zeichnungen

