

FBC PA M12 MA-FMA 5M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The most reliable way of achieving connections between two I/O slaves or between the control and one I/O subscriber is by way of pre-assembled cables. The line of cables covers PROFIBUS, CANopen, DeviceNet™, EtherCAT and Ethernet.

General ordering data

Version	Bus line, Connecting line, M12 / M12, Number of poles: 2, 5 m, pin, 90°; - socket 90°, Shielded: Yes, LED: No, Sheath material: PVC, Halogen: Yes
Order No.	1076550500
Type	FBC PA M12 MA-FMA 5M
GTIN (EAN)	4032248834181
Qty.	1 pc(s).

Creation date March 13, 2023 11:53:24 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

FBC PA M12 MA-FMA 5M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 415 g

Technical specifications for cable

Bending radius, min., moving	8 x cable diameter	Bending radius, min., stationary	8 x cable diameter
Cable length	5 m	Colour coding	red, green
Configurable cable length	No	Core cross-section	1 mm ²
Halogen	Yes	Hybrid cable	No
Insulation	PE	Irradiation crosslinked	No
Number of poles	2	Outside diameter	8 mm ± 0.4 mm
Resistant to welding beads	No	Sheath material	PVC
Sheathing colour	black	Shielded	Yes
Suitable for cable carriers	No	Temperature range, moving	-5...60 °C
Temperature range, stationary	-30...80 °C	Welding spark resistance	No

General technical data

Coding	A	Connection thread	M12 / M12
Contact surface	Gold-plated	Housing main material	PUR
Insulation strength	10 ⁸ Ω	LED	No
Plugging cycles	≥ 100	Pollution severity	3
Protection degree	IP67	Rated voltage	100 V
Temperature range of housing	-25...+80 °C	Threaded ring material	Brass, nickel-plated
Tightening torque	M12: 0.8 - 1.2 Nm	Version	pin, 90°; - socket 90°;
jumpered	No		

Electrical properties

Insulation strength 10⁸ Ω Rated voltage 100 V

Classifications

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ECLASS 9.0	27-06-03-08
ECLASS 9.1	27-06-03-08	ECLASS 10.0	27-06-03-08
ECLASS 11.0	27-06-03-08	ECLASS 12.0	27-06-03-08

Environmental Product Compliance

REACH SVHC Lead 7439-92-1
 SCIP 273a2adc-147a-4b75-9d50-227deee55a05

Approvals

Approvals



ROHS Conform

FBC PA M12 MA-FMA 5M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Downloads**

Engineering Data	WSCAD
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN

FBC PA M12 MA-FMA 5M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com


Drawings

Dimensioned drawing




Male, angled

Pole scheme




Pin

Wiring diagram




Dimensioned drawing



Socket angled

Pole scheme



Socket

The ideal tool: Screwty® with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F