

IE-KSF-PKV14M-KLROB-6M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables

General ordering data

Version	
Order No.	1103660060
Type	IE-KSF-PKV 14M-KLROB-6M
GTIN (EAN)	4050118000108
Qty.	1 Stück

Erstellungs-Datum May 24, 2023 1:34:43 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

IE-KSF-PKV14M-KLROB-6M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 835 g

Temperatures

Operating temperature -40 °C...70 °C Operating temperature, min. -40 °C
 Operating temperature, max. 70 °C

Electrical properties

Operating voltage 30 V

General standards

Connector standard IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14

Standards

Connector standard IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14

Cable structure

Sheath diameter, max. 9.3 mm Sheathing colour black (similar to RAL 9005)

Electrical properties of cable

Operating voltage 30 V

Mechanical and material properties of cable

Min. bending radius, once only 5 x cable diameter Min. bending radius, repetitive 10 x cable diameter

Classifications

ETIM 6.0	EC001579	ETIM 7.0	EC001579
ETIM 8.0	EC001579	ECLASS 9.0	27-06-24-90
ECLASS 9.1	27-06-24-00	ECLASS 10.0	27-06-05-01
ECLASS 11.0	27-06-05-01	ECLASS 12.0	27-06-05-01

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Approvals

ROHS Conform

IE-KSF-PKV14M-KLROB-6M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Downloads


User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN

IE-KSF-PKV14M-KLROB-6M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen



Pin	Color	Pair
1	Blue	PAIR 1 (ST)
2	Orange	PAIR 1 (ST)
3	Green	PAIR 1 (ST)
4	Red	PAIR 1 (ST)
5	Black	PAIR 1 (ST)
6	White	PAIR 1 (ST)
7	Blue	PAIR 1 (ST)
8	Orange	PAIR 1 (ST)
9	Green	PAIR 1 (ST)
10	Red	PAIR 1 (ST)