

IE-KSF-PKV14M-KLROB-40M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables

General ordering data

Version	
Order No.	1103660400
Type	IE-KSF-PKV 14M-KLROB-40M
GTIN (EAN)	4050118011616
Qty.	1 Stück

Erstellungs-Datum May 24, 2023 1:36:21 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

IE-KSF-PKV14M-KLROB-40M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 4,890 g

Temperatures

Operating temperature -40 °C...70 °C Operating temperature, min. -40 °C
 Operating temperature, max. 70 °C

Electrical properties

Operating voltage 30 V

General standards

Connector standard IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14

Standards

Connector standard IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14

Cable structure

Sheath diameter, max. 9.3 mm Sheathing colour black (similar to RAL 9005)

Electrical properties of cable

Operating voltage 30 V

Mechanical and material properties of cable

Min. bending radius, once only 5 x cable diameter Min. bending radius, repetitive 10 x cable diameter

Classifications

ETIM 6.0	EC001579	ETIM 7.0	EC001579
ETIM 8.0	EC001579	ECLASS 9.0	27-06-24-90
ECLASS 9.1	27-06-24-00	ECLASS 10.0	27-06-05-01
ECLASS 11.0	27-06-05-01	ECLASS 12.0	27-06-05-01

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Approvals

ROHS Conform

IE-KSF-PKV14M-KLROB-40M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Downloads


User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN

IE-KSF-PKV14M-KLROB-40M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen



Pin	Color	Definition
1	Blue	PAIR 1 (E)
2	Blue	PAIR 1 (E)
3	Blue	PAIR 1 (E)
4	Blue	PAIR 1 (E)
5	Blue	PAIR 1 (E)
6	Blue	PAIR 1 (E)
7	Blue	PAIR 1 (E)
8	Blue	PAIR 1 (E)
9	Blue	PAIR 1 (E)
10	Blue	PAIR 1 (E)
11	Blue	PAIR 1 (E)
12	Blue	PAIR 1 (E)
13	Blue	PAIR 1 (E)
14	Blue	PAIR 1 (E)