

IE-PIC-HYB-S-0,2-300

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Hybrid, 10-pole. Inserts for plug-in connectors
ver.1 /4 /5 /14

General ordering data

Version	Crimp contact, for plug insert, Hybrid
Order No.	1135 150000
Type	IE-PIC-HYB-S-0,2-300
GTIN (EAN)	40322489 15347
Qty.	300 pc(s).

Creation date March 7, 2023 4:32:17 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

IE-PIC-HYB-S-0,2-300**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 0.27 g

General data

Wire connection cross section, finely stranded, max.	0.2 mm ²	Wire connection cross section, finely stranded, min.	0.08 mm ²
--	---------------------	--	----------------------

Electrical properties

Rated voltage 24 V

Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ECLASS 9.0	27-44-03-90
ECLASS 9.1	27-44-09-90	ECLASS 10.0	27-44-03-90
ECLASS 11.0	27-44-03-90	ECLASS 12.0	27-44-03-90

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Approvals

Approvals



ROHS Conform

Downloads

User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN Designation key / Type key
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-PIC-HYB-S-0,2-300

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings**Dimensioned drawing**