

H0,34/15 ZH TK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- supplied loose in polybag
- Weidmüller colour code

General ordering data

Version	Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, Turquoise
Order No.	1139070000
Type	H0,34/15 ZH TK
GTIN (EAN)	403224892047 1
Qty.	500 pc(s).
Packaging	loose

Creation date March 7, 2023 4:54:55 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

H0,34/15 ZH TK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 0.084 g

Technical data

Description of article	Twin wire-end ferrule, turquoise	Version	Twin wire-end ferrule
------------------------	----------------------------------	---------	-----------------------

Wire-end ferrules

Collar height (A)	3.5 mm	Collar width (B)	2 mm
Conductor cross-section	0.34 mm ²	Contact surface diameter (D1)	1.2 mm
Contact surface length (L2)	8 mm	L1 in mm	15 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm
Stripping length	11 mm	Wire connection cross section AWG, max.	AWG 22

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E354986

Downloads

Engineering Data	CAD data – STEP
User Documentation	Technical information - EN Technical information - DE
Catalogues	Catalogues in PDF-format
Brochures	

H0,34/15 ZH TK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawing

