

**HDC CM ST M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Flexible and all-purpose – the proper solution for many applications**

ConCept is a modular system consisting of modules and frames. Together, they form a complete insert that can easily be integrated into an HDC housing.

The patented modular system allows you to put together individual connector variants.

A variety of modules for power, signal and data transmission are supplemented further by modules intended for pneumatics, and SC/LC cables.

The sturdy, one-piece module-frame design (optionally available in polycarbonate or die-cast zinc) and the integrated module-release aid both improve handling of the product.

**General ordering data**

Version	Heavy-duty connectors, HDC insert, ConCept module
Order No.	<a href="#">1157970000</a>
Type	HDC CM ST M
GTIN (EAN)	403224894548 1
Qty.	1 pc(s).

## HDC CM ST M

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	37.5 mm	Height (inches)	1.476 inch
Width	22.8 mm	Width (inches)	0.898 inch
Length	34 mm	Length (inches)	1.339 inch
Net weight	21.4 g		

## Temperatures

Limit temperature	-40 °C ... 70 °C
-------------------	------------------

## ConCept Pneumatic module

Colour	beige	UL 94 flammability rating	V-0
--------	-------	---------------------------	-----

## Dimensions

Height of plug	37.5 mm	Total length base	34 mm
Width	22.8 mm		

## General data

Free from halogens	false	Insulation strength	$\leq 10^{10}$ m $\Omega$
Low smoke acc. DIN EN 45545-2	Yes	Material	Polycarbonate
Rated current (DIN EN 61984)	1 A	Rated impulse voltage (DIN EN 61984)	1 kV
Rated voltage (DIN EN 61984)	50 V	Series	ConCept module
Type	Pin	UL 94 flammability rating	V-0
Volume resistance	$\leq 20$ m $\Omega$		

## Version

Material	Polycarbonate	Volume resistance	$\leq 20$ m $\Omega$
----------	---------------	-------------------	----------------------

## Classifications

ETIM 6.0	EC002312	ETIM 7.0	EC002312
ETIM 8.0	EC002312	ECLASS 9.0	27-44-02-92
ECLASS 9.1	27-44-02-18	ECLASS 10.0	27-44-02-92
ECLASS 11.0	27-44-02-92	ECLASS 12.0	27-44-02-92

## Environmental Product Compliance

REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	1609748e-c278-4c9b-b3d1-e6215d2988cd

## Approvals

Approvals



ROHS	Conform
------	---------

**HDC CM ST M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a>