

**IL WMF2.5 BLZ OR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The plugs can be securely and easily fixed to the base terminal by using a locking element. The locking element avoids an unintentional disconnection of the plugs from the base terminal and ensures maximum safety.

**General ordering data**

Version	W-Series, Locking clips
Order No.	<a href="#">1167440000</a>
Type	IL WMF2.5 BLZ OR
GTIN (EAN)	4032248958474
Qty.	50 pc(s).

Creation date March 6, 2023 2:07:14 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

## IL WMF2.5 BLZ OR

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	28.85 mm	Depth (inches)	1.136 inch
Height	16.6 mm	Height (inches)	0.654 inch
Width	8.28 mm	Width (inches)	0.326 inch
Net weight	1.12 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

### Material data

Material	PA 66	Colour	orange
UL 94 flammability rating	V-2		

### General

Number of poles	2
-----------------	---

### Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	