

SAI-M23-KS-L-7/12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

General ordering data

Version	Sensor/Actuator plug-in connector, Empty enclosure
Order No.	1170270000
Type	SAI-M23-KS-L-7/12
GTIN (EAN)	4032248962259
Qty.	1 pc(s).

Creation date March 7, 2023 5:55:46 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

SAI-M23-KS-L-7/12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	82 g
------------	------

Temperatures

Operating temperature, min.	-40 °C	Operating temperature, max.	125 °C
-----------------------------	--------	-----------------------------	--------

Technical data customisable plug-in connectors

Cable diameter, max.	12 mm	Cable diameter, min.	7 mm
Housing main material	Copper-zinc alloy	Plugging cycles	> 1000
Pollution severity	3	Protection degree	IP67, IP69K
Shield connection	Yes	Temperature range of housing	-40...+125 °C

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC003556
ETIM 8.0	EC003556	ECLASS 9.1	27-44-02-02
ECLASS 10.0	27-44-02-24	ECLASS 11.0	27-44-02-24
ECLASS 12.0	27-44-02-24		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	1c533b66-fcff-4da5-b89f-fd55fbf5cb55

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E344862

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

Data sheet


SAI-M23-KS-L-7/12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings

Dimensioned drawing



Cable connector



F