

## ELS 6/30 K MC NE WS

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



ELS MultiCard markers can be printed with a PrintJet, plotter or SMark printer. In particular, colour printing with PrintJet AVANCED allows the eye-catching identification marking of cables and terminal strips in many ways.

ELS 6/30 for use in the WKM 8/30 cable markers or in the EM8/30 group-tag carriers

ELS 7/40 for use in the SchT5S group-tag carriers

ELS 16/40 for use in the WKM 18/43 cable markers or the SchT5 group-tag carriers

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

Version	ELS, Insert markers, 30 x 6 mm, white
Order No.	<a href="#">1191390000</a>
Type	ELS 6/30 K MC NE WS
GTIN (EAN)	4032248974177
Qty.	80 pc(s).
compatible printer	<a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a>

Creation date May 4, 2023 5:24:08 PM CEST

Catalogue status 28.04.2023 / We reserve the right to make technical changes.

## ELS 6/30 K MC NE WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	0.8 mm	Depth (inches)	0.031 inch
Height	30 mm	Height (inches)	1.181 inch
Width	6 mm	Width (inches)	0.236 inch
Net weight	0.813 g		

### Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

### General data

Colour	white	Halogen	No
Material	Polyamide 66	Number of markers per combination	1 MultiCard = Insert markers
Number per sheet	16	Operating temperature range	-40...100 °C
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
UL 94 flammability rating	V-2	Version	Self-adhesive
Width	6 mm		

### Conductor and cable markers

Halogen	No
---------	----

### Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Product Change Notification	<a href="#">Technical change to MultiCard material - DE</a> <a href="#">Technical change to MultiCard material - EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Data sheet**

**ELS 6/30 K MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

