

**VGM40-SS68 20-32 BG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

**General ordering data**

Version	Heavy-duty connectors, Accessories, Cable glands, Stainless steel 1.4305 (303)
Order No.	<a href="#">1193590000</a>
Type	VGM40-SS68 20-32 BG
GTIN (EAN)	4032248976614
Qty.	10 pc(s).

Creation date March 7, 2023 6:01:06 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

**VGM40-SS68 20-32 BG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Length	43 mm	Length (inches)	1.693 inch
Net weight	166.4 g		

**Temperatures**

Limit temperature	-40 °C ... 130 °C
-------------------	-------------------

**General information**

AF size	45 mm	Cable glands	M 40
External thread	M 40	Length of thread	8 mm
Material	Stainless steel 1.4305 (303)	O-Ring	Silicone
Protection degree	IP68 - 15 bar	Standards	EN 45545-2:2013
UL 94 flammability rating	V-0		

**Classifications**

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32	ECLASS 12.0	27-14-08-01

**Approvals**

Approvals



ROHS Conform

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>