

VGM40/1-SS68 20-32 BG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	Heavy-duty connectors, Accessories, Cable glands, Stainless steel 1.4305 (303)
Order No.	1205920000
Type	VGM40/1-SS68 20-32 BG
GTIN (EAN)	4032248987825
Qty.	10 pc(s).

Creation date March 7, 2023 6:03:00 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

VGM40/1-SS68 20-32 BG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Length	82 mm	Length (inches)	3.228 inch
Net weight	323.6 g		

Temperatures

Limit temperature	-40 °C ... 130 °C
-------------------	-------------------

General information

AF size	45 mm	Cable glands	M 40
External thread	M 40	Length of thread	8 mm
Material	Stainless steel 1.4305 (303)	O-Ring	Silicone
Protection degree	IP68 - 15 bar	Standards	EN 45545-2:2013
UL 94 flammability rating	V-0		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32	ECLASS 12.0	27-14-08-01

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN