

IE-PS-SCRJ1-POF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

FO SC-RJ plug-in connectors according to IEC 61754-24
for wire outer diameters 2.6 to 3 mm

General ordering data

Version	FO connector, Plug SCRJ, POF, IP20
Order No.	1206720000
Type	IE-PS-SCRJ1-POF
GTIN (EAN)	4032248988570
Qty.	10 Stück

Erstellungs-Datum May 30, 2023 11:18:53 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

IE-PS-SCRJ1-POF

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	51 mm	Depth (inches)	2.008 inch
Height	14.7 mm	Height (inches)	0.579 inch
Width	8.95 mm	Width (inches)	0.352 inch
Net weight	17.9 g		

Temperatures

Operating temperature	-20 °C...80 °C	Operating temperature, min.	-20 °C
Operating temperature, max.	80 °C	Humidity	0...93 % rel. humidity

General data

Bending protection sleeve material	TPE	Cable pull-out force, min.	100 N
Colour	yellow, black	Connection 1	SCRJ
Connection 2	Rapid connection system: crimping, cutting	Crimp barrel material	Copper, nickel-plated
Description of article	Plug SCRJ, POF	Dust protection cap material	TPE
Ferrule material	Nickel silver	Fibre type	POF
Housing main material	PC UL 94 V0	Housing material, insert	Zinc diecast, nickel-plated
Humidity	0...93 % rel. humidity	Insertion loss	≤ 1.0 dB
Plugging cycles	1000	Pressure spring material	Stainless steel, rust-proof
Protection degree	IP20	Single conductor diameter, max	2.3 mm
Single conductor diameter, min	2.1 mm		

General standards

Certificate No. (UL)	E477798	Connector standard	IEC 61754-24
----------------------	---------	--------------------	--------------

Classifications

ETIM 6.0	EC001122	ETIM 7.0	EC001122
ETIM 8.0	EC001122	ECLASS 9.0	19-17-01-22
ECLASS 9.1	19-17-01-22	ECLASS 10.0	19-17-01-22
ECLASS 11.0	19-17-01-22	ECLASS 12.0	19-17-01-22

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UL)	E477798

IE-PS-SCRJ1-POF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Downloads

Approval/Certificate/Document of Conformity	PROFINET Manufacturer's Declaration
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN Manual
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-PS-SCRJ1-POF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

Dimensioned drawing

