

**IE-PS-SCRJ1-MM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



FO SC-RJ plug-in connectors according to IEC 61754-24  
for wire outer diameters 2.6 to 3 mm

**General ordering data**

Version	FO connector, Plug SCRJ, multimode, IP20
Order No.	<a href="#">1206730000</a>
Type	IE-PS-SCRJ1-MM
GTIN (EAN)	4032248988587
Qty.	10 Stück

Erstellungs-Datum May 30, 2023 11:19:03 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

## IE-PS-SCRJ1-MM

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	51 mm	Depth (inches)	2.008 inch
Height	14.7 mm	Height (inches)	0.579 inch
Width	8.95 mm	Width (inches)	0.352 inch
Net weight	1.1 g		

### Temperatures

Operating temperature	-20 °C...80 °C	Operating temperature, min.	-20 °C
Operating temperature, max.	80 °C	Humidity	0...93 % rel. humidity

### General data

Bending protection sleeve material	TPE	Cable pull-out force, min.	100 N
Colour	Miscellaneous	Connection 1	SCRJ
Connection 2	gluing, crimping, polishing	Crimp barrel material	Copper, nickel-plated
Description of article	Plug SCRJ, multimode	Dust protection cap material	TPE
Ferrule material	Zirconia	Fibre type	GOF, Multimode
Housing main material	PC UL 94 V0	Housing material, insert	Zinc diecast
Humidity	0...93 % rel. humidity	Insertion loss	≤ 0.4 dB
Plugging cycles	1000	Pressure spring material	Stainless steel, rust-proof
Protection degree	IP20	Return loss (attenuation)	≥ 30 dB
Sheath diameter, max.	3 mm	Sheath diameter, min.	2.8 mm
Single conductor diameter, max	1.4 mm	Single conductor diameter, min	0.6 mm

### General standards

Certificate No. (UL)	E477798	Connector standard	IEC 61754-24
----------------------	---------	--------------------	--------------

### Classifications

ETIM 6.0	EC001122	ETIM 7.0	EC001122
ETIM 8.0	EC001122	ECLASS 9.0	19-17-01-22
ECLASS 9.1	19-17-01-22	ECLASS 10.0	19-17-01-22
ECLASS 11.0	19-17-01-22	ECLASS 12.0	19-17-01-22

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	4f3aae94-c2bc-4010-b63b-5b114ba6bd55

### Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UL)	E477798

## IE-PS-SCRJ1-MM

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">PROFINET Manufacturer's Declaration</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>

**IE-PS-SCRJ1-MM**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

**Dimensioned drawing**

