

CLI R 1-12 RT TRIP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

General ordering data

Version	CableLine, Mounting mandrel
Order No.	1208940000
Type	CLI R 1-12 RT TRIP
GTIN (EAN)	4032248990337
Qty.	10 Stück

Erstellungs-Datum May 25, 2023 12:21:01 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

CLI R 1-12 RT TRIP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	1.9 g
------------	-------

Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

General data

Colour	To customer specification	Colour of printing	black
Halogen	Yes	Material	PVC, soft, without Cadmium
Number per mandrel	5	Operating temperature range	-30...80 °C
Operating temperature range, max.	80 °C	Operating temperature range, min.	-30 °C
Orientation of print	horizontal	Printed characters	Mixed characters
Printing method	hot-embossing	Type of printing	To customer specification
UL 94 flammability rating	V-0	Version	MultiPack

Conductor and cable markers

Conductor O.D.	2.5 - 5 mm	Conductor O.D., max.	5 mm
Conductor O.D., min.	2.5 mm	Conductor cross-section, max.	4 mm ²
Conductor cross-section, min.	1.5 mm ²	Cross-section for connected wire	1.5 - 4 mm ²
Halogen	Yes		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Product Change Notification	PCN CableLine_DE PCN CableLine_EN
Catalogues	Catalogues in PDF-format