

VP M40 EXE MS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	VPMS Ex (ex blanking plug, brass), Blanking plug, in closed state, M 40, 15 mm, Brass, nickel-plated
Order No.	1210930000
Type	VP M40 EXE MS
GTIN (EAN)	4032248992430
Qty.	10 Stück

Erstellungs-Datum May 25, 2023 12:21:39 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

VP M40 EXE MS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Length	19 mm	Length (inches)	0.748 inch
Diameter	40 mm	Wall thickness, max.	14 mm
Net weight	115.2 g		

Temperatures

Operating temperature	-40 °C...100 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	100 °C		

Certificate numbers cable gland

Certificate no. cable gland (ATEX)	INERIS 09 ATEX 0059X	Identification	II 2 GD, Ex d IIC, Ex e II, Ex tD
------------------------------------	----------------------	----------------	-----------------------------------

General information

AF size 1	45 mm	Diameter of sealing ring	40 mm
External thread	M 40	Halogen	Yes
Length of thread	15 mm	Material	Brass, nickel-plated
O-Ring	NBR	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Protection degree	IP54, IP64, IP68	Silicone	No
Torque for cap nut, max.	13.2 Nm	Torque for cap nut, min.	8.8 Nm
Torque for connecting adapter, max.	44 Nm	Torque for connecting adapter, min.	22 Nm

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ECLASS 9.0	27-14-44-25
ECLASS 9.1	27-14-44-35	ECLASS 10.0	27-14-44-25
ECLASS 11.0	27-14-44-25	ECLASS 12.0	27-14-08-05

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1; 96-45-7 Imidazolidine-2-thione
SCIP	Oc0edf9f-b35a-4d1f-b8f0-99d4b22ac203

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format

VP M40 EXE MS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

