

IE-SFP-1GLHXLC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

- Supports DDM (Digital Diagnostic Monitoring)
- IEEE 802.3z compliant (Gigabit Ethernet SFPs)
- IEEE 802.3u compliant (Fast Ethernet SFPs)
- Symmetric LVPECL I/Os (Gigabit Ethernet SFPs)
- Symmetric PECL I/Os (Fast Ethernet SFPs)
- TTL signal detection indicator
- Pluggable in operation (hot pluggable)
- Class 1 laser product, EN60825-1 compliant
- Applicable for switches of the Basic-, Value- and PremiumLine

General ordering data

Version	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 40 km, 0 °C...60 °C
Order No.	1241520000
Type	IE-SFP-1GLHXLC
GTIN (EAN)	4050118029369
Qty.	1 pc(s).

Creation date March 7, 2023 7:08:08 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

IE-SFP-1GLHXLC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 36 g

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	0 °C...60 °C
Operating temperature, min.	0 °C	Operating temperature, max.	60 °C
Humidity	5 to 95 % (non-condensing)		

EMC conformity and approvals

EMC standards	EN 55032, EN 55024	Safety standard	UL 60950-1
Ship use	DNV-GL		

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	60 °C
Operating temperature, min.	0 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Fibre optic transceiver characteristics

Transmission rate	1000 Mbps	
Digital diagnostic monitor function (DDM)	Supported	
Transceiver type	Singlemode	
Connector type	LC-Duplex	
Transmission distance, typ.	40 km	
Wavelength	typ.	1,310 nm
	Wavelength	TX
	min.	1,280 nm
	max.	1,340 nm
	Wavelength	RX
	min.	1,260 nm
Receive power	min.	-24 dBm
	max.	-1 dBm
Transmission power	min.	-4 dBm
	max.	3 dBm
Link-budget	20 dB	

Guarantee

Time interval 3 years

Power supply

Voltage supply 3.3 V (via Ethernet switch)

Technical data

Type of mounting Insert in SFP slot

Creation date March 7, 2023 7:08:08 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

IE-SFP-1GLHXLC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Classifications**

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ECLASS 9.0	27-44-03-92	ECLASS 9.1	27-44-02-92
ECLASS 10.0	27-44-03-92	ECLASS 11.0	27-44-03-92
ECLASS 12.0	27-44-03-92		

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E230683

Downloads

Approval/Certificate/Document of Conformity	DNV certificate EU Declaration of Conformity UK Declaration of Conformity
Catalogues	Catalogues in PDF-format
Brochures	