

KLBUE 3-8 FM4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Similar to illustration

Thanks to special mounting feet, the product portfolio also includes shield clamping saddles that can be mounted on the TS 35 DIN rail. The shield is diverted from the shield clamping saddles via the mounting foot to the TS 35 mounting rail and thus to PE (ground).

General ordering data

Version	Clamping yoke
Order No.	1252530000
Type	KLBUE 3-8 FM4
GTIN (EAN)	4032248112531
Qty.	10 Stück

Erstellungs-Datum May 30, 2023 11:31:31 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

KLBUE 3-8 FM4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	26 mm	Depth (inches)	1.024 inch
Height	50 mm	Height (inches)	1.969 inch
Width	14.5 mm	Width (inches)	0.571 inch
Net weight	17.2 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Colour	silver
--------	--------

System specifications

Rail	TS 35
------	-------

Additional technical data

Explosion-tested version	No
--------------------------	----

Conductors for clamping (rated connection)

Cable diameter, max.	8 mm	Cable diameter, min.	3 mm
----------------------	------	----------------------	------

General

Rail	TS 35
------	-------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ECLASS 9.0	27-14-11-50
ECLASS 9.1	27-14-11-50	ECLASS 10.0	27-14-11-50
ECLASS 11.0	27-14-11-50	ECLASS 12.0	27-14-11-50

Approvals

Approvals	
-----------	---

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	EAC certificate
Engineering Data	CAD data – STEP
Engineering Data	WSCAD, EPLAN
User Documentation	Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

Erstellungs-Datum May 30, 2023 11:31:31 AM CEST