

IE-FPOZ2EE0005MSJ0SJO-X**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Assembled IE cables, FO patch cable, POF, SC-RJ - SC-RJ,
black

General ordering data

Version	Connecting line, PROFINET, SCRJ IP 20, SCRJ IP 20, 980 µm, 5 m
Order No.	1273430050
Type	IE-FPOZ2EE0005MSJ0SJO-X
GTIN (EAN)	4050118062878
Qty.	1 Stück

IE-FPOZ2EE0005MSJ0SJO-X

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Length	5 m	Length (inches)	196.85 inch
Net weight	62 g		

Temperatures

Operating temperature	-20 °C...80 °C	Operating temperature, min.	-20 °C
Operating temperature, max.	80 °C		

Cable structure

Cable layout	ZIPCORD	Core diameter	980 µm
Insulation	PE	Number of wires	2
Sheath diameter	2.2*4.5 mm	Sheathing colour	black

Mechanical and material properties of cable

Bending cycles	10.000	Halogen	No
Min. bending radius, once only	25 mm	Min. bending radius, repetitive	25 mm
Pulling force	≤ 160 N		

Plug

Plug	Cable side	left	
	Version of contact face	SC-RJ	
	Protection degree (IP)	IP20	
	Gender of contact	male contact	
	Outlet direction	straight	
	Version of connector	plug	
	Housing main material	Plastic	
	Status indicator available	No	
	Shielding available	No	
	Cable side	right	
	Version of contact face	SC-RJ	
	Protection degree (IP)	IP20	
	Gender of contact	male contact	
	Outlet direction	straight	
	Version of connector	plug	
	Housing main material	Plastic	
	Status indicator available	No	
	Shielding available	No	
	Plug left	SC-RJ, IP20, male contact, straight, plug, Plastic, unshielded	
	Plug right	SC-RJ, IP20, male contact, straight, plug, Plastic, unshielded	

Plug, left

Connector left	Plug left	SC-RJ, IP20, male contact, straight, plug, Plastic, unshielded
	SCRJ IP 20	

Plug, right

Connector right	Plug right	SC-RJ, IP20, male contact, straight, plug, Plastic, unshielded
	SCRJ IP 20	

Erstellungs-Datum May 22, 2023 2:14:17 PM CEST

IE-FPOZ2EE0005MSJ0SJO-X

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Classifications

ETIM 6.0	EC002607	ETIM 7.0	EC002607
ETIM 8.0	EC002607	ECLASS 9.0	27-06-10-03
ECLASS 9.1	27-06-10-03	ECLASS 10.0	27-06-10-03
ECLASS 11.0	27-06-10-03	ECLASS 12.0	27-06-10-03

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	PROFINET Manufacturer's Declaration
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-FPOZ2EE0005MSJ0SJO-X

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Zeichnungen

Detailed drawing

