

SDIK PH2 SL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Version	Screwdriver, Screwdriver
Order No.	1274720000
Type	SDIK PH2 SL
GTIN (EAN)	4050118073232
Qty.	1 Stück
Delivery status	This article will no longer be available in the future.
Available until	2021-08-06
Alternative product	2749660000

Erstellungs-Datum May 30, 2023 11:32:58 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

SDIK PH2 SL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Width	218 mm	Width (inches)	8.583 inch
Diameter	36 mm	Net weight	98 g

Technical data

Description of article	VDE-insulated crosshead screwdriver, Phillips size 2, SlimLine
------------------------	--

Screwing tools

Blade length	100 mm	Blade size, crosshead	Gr. PH2
Form	Crosshead	Size	2

Classifications

ETIM 6.0	EC000144	ETIM 7.0	EC000144
ETIM 8.0	EC000144	ECLASS 9.0	21-04-04-06
ECLASS 9.1	21-04-04-06	ECLASS 10.0	21-04-04-06
ECLASS 11.0	21-04-04-06	ECLASS 12.0	21-04-04-06

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

Approvals

Approvals



Downloads

Approval/Certificate/Document of Conformity	Manufacturer's Declaration - Screwdrivers
Catalogues	Catalogues in PDF-format
Brochures	

SDIK PH2 SL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
www.weidmueller.com

Zeichnungen

Example of use