

IE-SCRJ-IP67-POF-100

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



FO SC inserts for plug-in connectors ver.1 / 4 / 14

General ordering data

Version	FO connector, Replacement crimp barrel, IP67 with housing
Order No.	1278430000
Type	IE-SCRJ-IP67-POF-100
GTIN (EAN)	4050118069136
Qty.	100 Stück

Erstellungs-Datum May 25, 2023 12:24:05 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

IE-SCRJ-IP67-POF-100

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	26.5 mm	Depth (inches)	1.043 inch
Height	5.8 mm	Height (inches)	0.228 inch
Net weight	3 g		

General data

Colour	Miscellaneous	Connection 1	SCRJ
Connection 2	Rapid connection system: crimping, cutting	Description of article	Replacement crimp barrel
Ferrule material	Nickel silver	Fibre type	POF
Insertion loss	≤ 1.0 dB	Protection degree	IP67 with housing

Classifications

ETIM 6.0	EC001122	ETIM 7.0	EC001122
ETIM 8.0	EC001122	ECLASS 9.0	19-17-01-22
ECLASS 9.1	19-17-01-22	ECLASS 10.0	19-17-01-22
ECLASS 11.0	19-17-01-22	ECLASS 12.0	19-17-01-22

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Approvals

Approvals



ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	PROFINET Manufacturer's Declaration
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN Designation key / Type key
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN