

**ETA 1170 21 10A****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Weidmueller offer circuit breakers for the integration of our fuse terminals for automotive fuses with a range from 100 mA to 25 A.

**General ordering data**

Version	Accessories, Circuit breaker, 10 A
Order No.	<a href="#">1278790000</a>
Type	ETA 1170 21 10A
GTIN (EAN)	4050118091281
Qty.	5 pc(s).

Creation date March 7, 2023 7:39:32 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

## ETA 1170 21 10A

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	51.6 mm	Depth (inches)	2.031 inch
Height	22 mm	Height (inches)	0.866 inch
Width	9.8 mm	Width (inches)	0.386 inch
Net weight	10 g		

## Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C
----------------------------------	--------	----------------------------------	--------

## Material data

Colour	black
--------	-------

## System specifications

Version	Fuse cartridge
---------	----------------

## Additional technical data

Installation advice	Direct mounting	Type of mounting	Plugged
---------------------	-----------------	------------------	---------

## Fuse cartridges

Colour	black	Current	10 A
Version	Fuse cartridge		

## General

Installation advice	Direct mounting
---------------------	-----------------

## Rating data

Rated voltage	28 V DC	Rated current	10 A
---------------	---------	---------------	------

## Classifications

ETIM 6.0	EC000035	ETIM 7.0	EC000035
ETIM 8.0	EC002704	ECLASS 9.0	27-14-20-01
ECLASS 9.1	27-14-20-01	ECLASS 10.0	27-14-20-01
ECLASS 11.0	27-14-20-01	ECLASS 12.0	27-14-20-01

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">WSCAD</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>