

**ETA 1180 01 0.2A****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Similar to illustration

Weidmueller offer circuit breakers for the integration of our fuse terminals for automotive fuses with a range from 100 mA to 25 A.

**General ordering data**

|            |                                     |
|------------|-------------------------------------|
| Version    | Accessories, Circuit breaker, 0.2 A |
| Order No.  | <a href="#">1278850000</a>          |
| Type       | ETA 1180 01 0.2A                    |
| GTIN (EAN) | 4050118091458                       |
| Qty.       | 5 pc(s).                            |

Creation date March 7, 2023 7:40:22 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

## ETA 1180 01 0.2A

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 52.3 mm | Depth (inches)  | 2.059 inch |
| Height     | 24.4 mm | Height (inches) | 0.961 inch |
| Width      | 8.2 mm  | Width (inches)  | 0.323 inch |
| Net weight | 10.6 g  |                 |            |

## Material data

|        |       |
|--------|-------|
| Colour | black |
|--------|-------|

## System specifications

|         |                |
|---------|----------------|
| Version | Fuse cartridge |
|---------|----------------|

## Additional technical data

|                     |                 |                  |         |
|---------------------|-----------------|------------------|---------|
| Installation advice | Direct mounting | Type of mounting | Plugged |
|---------------------|-----------------|------------------|---------|

## Fuse cartridges

|         |                |         |       |
|---------|----------------|---------|-------|
| Colour  | black          | Current | 0.2 A |
| Version | Fuse cartridge |         |       |

## General

|                     |                 |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

## Rating data

|               |         |               |       |
|---------------|---------|---------------|-------|
| Rated voltage | 64 V DC | Rated current | 0.2 A |
|---------------|---------|---------------|-------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000035    | ETIM 7.0    | EC000035    |
| ETIM 8.0    | EC002704    | ECLASS 9.0  | 27-14-20-01 |
| ECLASS 9.1  | 27-14-20-01 | ECLASS 10.0 | 27-14-20-01 |
| ECLASS 11.0 | 27-14-20-01 | ECLASS 12.0 | 27-14-20-01 |

## Environmental Product Compliance

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                    |   |
|--------------------|---|
| Engineering Data   | <a href="#">CAD data – STEP</a>                 |
| Engineering Data   | <a href="#">WSCAD</a>                           |
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>        |