

ETA 1180 01 0.7A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Similar to illustration

Weidmueller offer circuit breakers for the integration of our fuse terminals for automotive fuses with a range from 100 mA to 25 A.

General ordering data

Version	Accessories, Circuit breaker, 0.7 A
Order No.	1278930000
Type	ETA 1180 01 0.7A
GTIN (EAN)	4050118091519
Qty.	5 pc(s).

Creation date March 7, 2023 7:41:19 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

ETA 1180 01 0.7A

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	52.3 mm	Depth (inches)	2.059 inch
Height	24.4 mm	Height (inches)	0.961 inch
Width	8.2 mm	Width (inches)	0.323 inch
Net weight	10.6 g		

Material data

Colour	black
--------	-------

System specifications

Version	Fuse cartridge
---------	----------------

Additional technical data

Installation advice	Direct mounting	Type of mounting	Plugged
---------------------	-----------------	------------------	---------

Fuse cartridges

Colour	black	Current	0.7 A
Version	Fuse cartridge		

General

Installation advice	Direct mounting
---------------------	-----------------

Rating data

Rated voltage	64 V DC	Rated current	0.7 A
---------------	---------	---------------	-------

Classifications

ETIM 6.0	EC000035	ETIM 7.0	EC000035
ETIM 8.0	EC002704	ECLASS 9.0	27-14-20-01
ECLASS 9.1	27-14-20-01	ECLASS 10.0	27-14-20-01
ECLASS 11.0	27-14-20-01	ECLASS 12.0	27-14-20-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format