

CB-DM 200/4,5 NC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Fastening of cables or bundles with ties into electrical switchgears and cabinets.

General ordering data

Version	Cable ties, 4.5 x 203 mm, Plastic, 220 N
Order No.	1279300000
Type	CB-DM 200/4,5 NC
GTIN (EAN)	4008 190 185930
Qty.	100 Stück

Erstellungs-Datum May 30, 2023 11:34:15 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

CB-DM 200/4,5 NC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	2 mm	Depth (inches)	0.079 inch
Height	203 mm	Height (inches)	7.992 inch
Width	4.5 mm	Width (inches)	0.177 inch
Net weight	1.44 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Installation materials

Bundle diameter, max.	50 mm	Bundle diameter, min.	3 mm
Cable diameter, max.	50 mm	Diameter of fastening hole	6.3 mm
For re-opening	No	Material	Plastic
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Tensile strength	220 N	Tensile strength (Pound-force)	49 lbf
UL 94 flammability rating	V-2	UV-resistant	No
Version	for cable harnesses		

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02	ECLASS 12.0	27-14-07-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format